








RP-QII/QIII series pump head compatibility

Please select the pump head that suits your pump, tube material, tube diameter, etc.

Part Number	RK-QII1.5S	RK-QIII1.5S-D	RK-QIIP5F	RK-QIIP5F-A	RK-QIIP5S	RK-QIIP5S-A	RK-QII1.2C
Tubing Material	Silicone	Silicone	PharMed® BPT	PharMed® BPT	Silicone	Silicone	SWFT
Tubing Diameter (mm)	I.D.1.5 × O.D.2.5	I.D.1.5 × O.D.2.5	I.D.0.5 × O.D.1.5	I.D.0.5 × O.D.1.5	I.D.0.5 × O.D.1.5	I.D.0.5 × O.D.1.5	I.D.1.2 × O.D.2.5
Tubing Length (mm)	60	80	60	80	60	80	60
Photo							

<Pump and pump head correspondence table>

Pump head Pump Model	RK-QII1.5S	RK-QIII1.5S-D	RK-QIIP5F	RK-QIIP5F-A	RK-QIIP5S	RK-QIIP5S-A	RK-QII1.2C
RP-QIIB/QIIB Stepper motor 1/150.95	Standard 0.35~350 μL/min	Standard 0.35~350 μL/min	Standard 0.06~60 μL/min	Standard 0.06~60 μL/min	Standard 0.06~60 μL/min	Standard 0.06~60 μL/min	Not available
RP-QIIC/QIIC Stepper motor 1/51.45	Standard 1.1~1100 μL/min	Standard 1.1~1100 μL/min	Standard 0.18~180 μL/min	Standard 0.18~180 μL/min	Standard 0.18~180 μL/min	Standard 0.18~180 μL/min	Not available
RP-QII/QIII DC motor 1/196	Standard 0.9 mL/min	Customizable 0.9 mL/min	Customizable 0.14 mL/min	Customizable 0.14 mL/min	Customizable 0.14 mL/min	Customizable 0.14 mL/min	Standard 0.45 mL/min
RP-QIIX/QIIX DC motor 1/75	Standard 2.2 mL/min	Customizable 2.2 mL/min	Customizable 0.32 mL/min	Customizable 0.32 mL/min	Customizable 0.32 mL/min	Customizable 0.32 mL/min	Standard 1.2 mL/min
RP-QIIA/QIIIA High-Speed DC motor 1/75	Standard 3 mL/min	Customizable 3 mL/min	Customizable 0.45 mL/min	Customizable 0.45 mL/min	Customizable 0.45 mL/min	Customizable 0.45 mL/min	Not available

※ PharMed® is a trademark of Saint-Gobain Performance Plastics.

※ Note: Details including specifications may change at any time without notification.

TFS (Takasago Fluidic Systems)

1900 West Park Drive, Suite 280, Westborough, MA 01581 U.S.A.

Tel: +1-508-983-1434 E-mail: info@takasago-fluidics.com

URL: <https://www.takasago-fluidics.com/>